





Like 8

ツイート 6

☎ 045-922-5221

English Site Map

製品

Furutoの技術力

ニュース

会社案内

採用情報

Home > Special > tape decontamination > Products



特集

Reconstruction assistance tape

Decontamination tape

Product introduction

Decontamination effect

How to use

Precautions for Use

How to get

Q & A

Product introduction

Developed the "tape decontamination" Hi-Tech Plaza Technical Assistance Center Iwaki Fukushima Prefecture.

Agree with this research and development, our company, but we have done to provide prototyping and product development in June 2011, this time, will be released from December 19 general this product.

This is an easy-to-use he concept in off easy "" just peel off stuck "by hand", does not require a special machine operations and difficult "and" get rid of the radioactive material adhering to the surface, even in households . is decontamination supplies that can be specifications of two types of tape for outdoor use:: (No. 8222 No.) (No. No. 8111), for indoor use.

Column



Tape for outdoor decontamination



No.8111: Product ID

Goods can also be used to place or effective in decontamination, such as playground equipment and part of the porch railing, can not use high-pressure washing machine is available.

PDF Download


Primary use

decontamination, such as ground-doorknob-sash playground equipment that is easy to touch people.

Standard size


Thickness (mm)	Width (mm)	Length (mm)
0.27mm	75mm	25M

Decontamination effect



福島県ハイテックプラザいわき建物屋上 (コンクリート) で測定
 ※測定値の一例であり、数値通り除染できることを保証するものではありません。

Tape for indoor decontamination



No.8222: Product ID

It is effective in the location of the hand touch, such as doorknobs and railings and carpet where dust tends to accumulate, such as top of the closet.

[PDF Download](#)


Primary use

carpet is easy to touch people, to decontamination, such as doorknobs, handrails

Standard size

Thickness (mm)	Width (mm)	Length (mm)
0.13mm	75mm	25M

Decontamination effect



福島県ハイテクプラザいわきのスチール製ロッカーの天板で測定
 ※測定値の一例であり、数値通り除染できることを保証するものではありません。

Unlike the pressure-sensitive adhesive tape for the purpose of sealing the Standard has been optimized for performance peeled off the surface contamination by improvements thickness of material and, waist, weight, thickness and nature of the adhesive fabric material tape We have also considered workability while wearing gloves when working further decontamination.

※ Not intended to lower values directly (micro sievert) dose equivalent, which is, generally speaking, this product is the goods that are intended rid itself of radioactive material is the cause of the radiation (decontaminated) that.

Inquiries about the tape decontamination

Inquiry about this product decontamination effect High-tech Fukushima Iwaki Technical Assistance Center

☎ 0246-44-1475

Inquiries about your order

☎ 0246-36-7153 Yoshima Iwaki factory orders Center